

29 September, 2022

Subject: Product Brand Consolidation Notification of Thermo Scientific™ Revco™, Forma™, and HERAFreeze™ Standard Performance ULT

Dear Channel Partners and Customers:

Please accept this letter as official notification regarding the consolidation of the Thermo Scientific Standard Performance (STP) series of Ultra Low freezers on **December 31st 2022**.

The platform is currently offered in four brands: Revco (RDE), Forma (FDE), HERAFreeze (HDE), and Thermo Scientific (TDE) and in two temperatures, -80 and -40. Starting January 1st 2023 all models will only be available in the Thermo Scientific (TDE) branding. A cross reference can be found in **Appendix A**.

There are no form, fit, or function differences between the brands except for brand labeling and inner door configurations. The Thermo Scientific TDE has a FOUR inner door configuration as standard, but can be ordered with a FIVE inner door configuration when ordered with the factory fitted option part numbers found in **Appendix B**. In addition, there is a FIVE inner door package code version that can be purchased, please note that these specific codes can't be configured with any other options, these codes can be found in **Appendix C**.

To identify models that replace the current product you are using, please contact your regional Thermo Scientific representative.

We stand behind our cold storage solutions, and the action to consolidate these brands is part of our program to continue delivering the best customer experience possible. We look forward to continuing to support your needs and assisting you through this exciting product transition.

Regards,

Chase Heibel
Senior Global Product Manager
Ultra Low Temperature Freezers

Thermo Fisher Scientific
275 Aiken Road | Asheville, NC 28804
Mobile +1 (650) 600-2203
chase.heibel@thermofisher.com | www.thermoscientific.com

APPENDIX A: Brand Cross Guide

-80 ULT

Cabinet Size	Power	FORMA	REVCO	HERAFREEZE	THERMO
300	115V, 60 Hz	FDE30086FA	RDE30086FA	HDE30086FA	TDE30086FA
	208-230V, 60 Hz	FDE30086FD	RDE30086FD	HDE30086FD	TDE30086FD
	230V, 50 Hz	FDE30086FV	RDE30086FV	HDE30086FV	TDE30086FV
	115V, 60 Hz	FDE30086LA	RDE30086LA	HDE30086LA	TDE30086LA
	208-230V, 60 Hz	FDE30086LD	RDE30086LD	HDE30086LD	TDE30086LD
	230V, 50 Hz	FDE30086LV	RDE30086LV	HDE30086LV	TDE30086LV
400	115V, 60 Hz	FDE40086FA	RDE40086FA	HDE40086FA	TDE40086FA
	208-230V, 60 Hz	FDE40086FD	RDE40086FD	HDE40086FD	TDE40086FD
	230V, 50 Hz	FDE40086FV	RDE40086FV	HDE40086FV	TDE40086FV
	115V, 60 Hz	FDE40086LA	RDE40086LA	HDE40086LA	TDE40086LA
	208-230V, 60 Hz	FDE40086LD	RDE40086LD	HDE40086LD	TDE40086LD
	230V, 50 Hz	FDE40086LV	RDE40086LV	HDE40086LV	TDE40086LV
500	115V, 60 Hz	FDE50086FA	RDE50086FA	HDE50086FA	TDE50086FA
	208-230V, 60 Hz	FDE50086FD	RDE50086FD	HDE50086FD	TDE50086FD
	230V, 50 Hz	FDE50086FV	RDE50086FV	HDE50086FV	TDE50086FV
	115V, 60 Hz	FDE50086LA	RDE50086LA	HDE50086LA	TDE50086LA
	208-230V, 60 Hz	FDE50086LD	RDE50086LD	HDE50086LD	TDE50086LD
	230V, 50 Hz	FDE50086LV	RDE50086LV	HDE50086LV	TDE50086LV
600	115V, 60 Hz	FDE60086EA	RDE60086EA	HDE60086EA	TDE60086FA
	208-230V, 60 Hz	FDE60086ED	RDE60086ED	HDE60086ED	TDE60086FD
	115V, 60 Hz	FDE60086FA	RDE60086FA	HDE60086FA	TDE60086FA
	208-230V, 60 Hz	FDE60086FD	RDE60086FD	HDE60086FD	TDE60086FD
	230V, 50 Hz	FDE60086FV	RDE60086FV	HDE60086FV	TDE60086FV
	115V, 60 Hz	FDE60086LA	RDE60086LA	HDE60086LA	TDE60086LA
	208-230V, 60 Hz	FDE60086LD	RDE60086LD	HDE60086LD	TDE60086LD
	230V, 50 Hz	FDE60086LV	RDE60086LV	HDE60086LV	TDE60086LV
	115V, 60 Hz	FDE60086MA	RDE60086MA	HDE60086MA	TDE60086LA

-40 ULT

Cabinet Size	Power	FORMA	REVCO	HERAFREEZE	THERMO
400	115V, 60 Hz	FDE40040FA	RDE40040FA	HDE40040FA	TDE40040FA
	208-230V, 60 Hz	FDE40040FD	RDE40040FD	HDE40040FD	TDE40040FD
	230V, 50 Hz	FDE40040FV	RDE40040FV	HDE40040FV	TDE40040FV
	115V, 60 Hz	FDE40040LA	RDE40040LA	HDE40040LA	TDE40040LA
	208-230V, 60 Hz	FDE40040LD	RDE40040LD	HDE40040LD	TDE40040LD
	230V, 50 Hz	FDE40040LV	RDE40040LV	HDE40040LV	TDE40040LV
500	115V, 60 Hz	FDE50040FA	RDE50040FA	HDE50040FA	TDE50040FA
	208-230V, 60 Hz	FDE50040FD	RDE50040FD	HDE50040FD	TDE50040FD
	230V, 50 Hz	FDE50040FV	RDE50040FV	HDE50040FV	TDE50040FV
	115V, 60 Hz	FDE50040LA	RDE50040LA	HDE50040LA	TDE50040LA
	208-230V, 60 Hz	FDE50040LD	RDE50040LD	HDE50040LD	TDE50040LD
	230V, 50 Hz	FDE50040LV	RDE50040LV	HDE50040LV	TDE50040LV
600	115V, 60 Hz	FDE60040FA	RDE60040FA	HDE60040FA	TDE60040FA
	208-230V, 60 Hz	FDE60040FD	RDE60040FD	HDE60040FD	TDE60040FD
	230V, 50 Hz	FDE60040FV	RDE60040FV	HDE60040FV	TDE60040FV
	115V, 60 Hz	FDE60040LA	RDE60040LA	HDE60040LA	TDE60040LA
	208-230V, 60 Hz	FDE60040LD	RDE60040LD	HDE60040LD	TDE60040LD
	230V, 50 Hz	FDE60040LV	RDE60040LV	HDE60040LV	TDE60040LV

APPENDIX B: 5 Inner Door Options - Configurable with other factory fitted options when ordered with 4 inner door Thermo Scientific TDE ULT.

Cabinet Size	Model	5 Inner Door Option
300	TDE300XXXX	5D300
400	TDE400XXXX	5D400
500	TDE500XXXX	5D500
600	TDE600XXXX	5D600

APPENDIX C: 5 Inner Door Options - Package code can't be configured with any other factory fitted options and is only available on the -80 ULT units.

Cabinet Size	5 Inner Door Package
300	TDE30086FV5ID
400	TDE40086FV5ID
500	TDE50086FV5ID
600	TDE60086FV5ID