



Whether you need to spin-down, shake, or stir, this bundle has you covered.

Get the full functionality of three machines in two pieces of equipment! Complete with a Fisherbrand Silicone Lab Mat to protect your workspace from spills and wear.

Fisherbrand Centrifuge/Stirrer

The industry's first high-speed centrifuge (12,500 rpm) and magnetic stirrer (3 L), combined into one unit. Made durable and chemically resistant with easy cleaning and maintenance-free operation. Its compact and low-profile design optimizes limited bench space and minimizes clutter in the lab.



Fisherbrand Mini Vortexer

Small footprint Vortexer offering maximum vortex shaking for a variety of tube sizes. A simple touch start operation allows for immediate sample mixing with one hand and automatic stop when tube is lifted.



Fisherbrand Silicone Lab Mat

This FDA food-grade silicone labmat is suitable for various laboratory settings, including cold rooms, clean rooms, and sterile suites, where high sterility is essential. Effectively safeguards countertops from temperatures up to 200°C (392°F) and demonstrates general chemical resistance to moderate oxidizing chemicals.



Reversible
Blue and Gray



Triple Instrument Bundle Item No. 120950

Fisherbrand Centrifuge/Stirrer

Colour	L x W x H in	L x W x H cm
Grey	9.2 x 7.3 x 4.7	23.5 x 18.5 x 12

Specifications: Centrifuge

Speed Range	500 – 999 rpm (increments of 1); 1,000 – 5,000 rpm (increments of 5); 5,000 – 12,500 rpm (increments of 25)
RCF	16 – 9,783 x g (max RCF calculated)
Run Time Ranges	30 seconds – 60 minutes (5 second increments)

Specifications: Magnetic Stirrer

Speed Range	50 – 999 rpm (increments of 1); 1,000 – 2,500 rpm (increments of 5)
Run Time Range	Stirrer Mode 30 seconds to 60 minutes or continuous (5 second increments)
	Oscillating Stirrer Mode 1 second – 60 minutes or continuous
Oscillating Period	30 seconds – 15 minutes
Capacity	3 L plus, Diameter of vessel not to exceed 130 mm



Package Includes

Centrifuge/Stirrer	Stirrer Rotor	12 Tube Adapters 0.2 mL & 0.5 mL
5.0 mL Tube Rotor	2 Stir Bars, 35 mm x 12 mm, cylindrical shape	
1.5/2.0 mL Tube Rotor	2 Silicone Mats for Stirrer Lid	
1 Low Voltage, Double Insulated Power Adapter (100-240 VAC, 50/60 Hz) with 4 Interchangeable Plugs		



Fisherbrand Mini Vortexer (17871672)

Colour	L x W x H in	L x W x H cm
Grey/Blue	5.1 x 4.3 x 3	13 x 11 x 7.5

Specifications

Speed	4,500 rpm
Orbit	6 mm
Capacity	Up to 50 mL tube



Package Includes

Mini Vortexer
2 Silicone Caps
1 Low Voltage, Double Insulated Power Adapter (100-240 VAC, 50/60 Hz) with 4 Interchangeable Plugs



Fisherbrand Silicone Lab Mat (15837944)

Colour	L x W x H in	L x W x H cm
Grey/Blue	14 x 23.5 x 0.1	35 x 60 x 0.2



Distributed by Fisher Scientific. Contact us today:

Austria: fishersci.at **Belgium:** fishersci.be **Denmark:** fishersci.dk
Germany: fishersci.de **Ireland:** fishersci.ie **Italy:** fishersci.it
Finland: fishersci.fi **France:** fishersci.fr **Netherlands:** fishersci.nl
Norway: fishersci.no **Portugal:** fishersci.pt **Spain:** fishersci.es
Sweden: fishersci.se **Switzerland:** fishersci.ch **UK:** fishersci.co.uk

© 2023 Thermo Fisher Scientific Inc. All rights reserved.
 Trademarks used are owned as indicated at fishersci.com/trademarks.